

Tolomatic Demo Kits - January 2018

All (except MXB Everything) Demo Kits have precut foam for safe transport in durable Pelican® suitcases
Kits 2192-0047 & 2190-0004 are operating demos (require 15A, 110Vac power)

	<p>RSA Electric Actuator and ACSI Integrated Servo Motor/Drive/Controller with PROFINET or EtherNet/IP Demo Includes:</p> <ol style="list-style-type: none"> 1. RSA24 SN04 SK6 RP1 actuator and ACSI 23-frame motor with integrated drive/controller 2. 5 Amp power supply 3. Three meter I/O, power and ethernet cables 4. USB Micro-B configuration cable 5. Case 	<p>PROFINET 3604-0040 or EtherNet/IP 3604-0039 Net Price \$1,150</p>
	<p>ERD - ACS Stepper Demo Includes:</p> <ol style="list-style-type: none"> 1. ERD06 with GD2 option Electric Actuator and motor 2. ERD10 with SS2 option Electric Actuator 3. ERD15 Electric Actuator with manual operation 4. ACS Stepper Drive 5. All needed cables 6. Case <p>Assembles into operating demo</p>	<p>2190-0004 Net Price \$995</p>
	<p>ERD - ACS Servo Demo Includes:</p> <ol style="list-style-type: none"> 1. ERD15 Reverse Parallel Electric Actuator and motor 2. ACS Servo Drive/Controller 3. Power Supply 4. All needed cables 5. Case <p>Assembles into operating demo</p>	<p>2192-0047 Net Price \$995</p>
	<p>Roller Screw Demo Includes:</p> <ol style="list-style-type: none"> 1. 20 x 5 Roller Screw sample with Armoloy coating 2. Case 	<p>2750-0189 Net Price \$875</p>

	MX Electric Demo Includes: <ol style="list-style-type: none"> 1. MXE25S Electric Screw-Drive Rodless Actuator 2. MXB25P & 25U Electric Belt-Drive Rodless Actuators 3. Ball & Solid Nut Screw samples, 6 Belt Material samples 4. Cross section of all MX extrusion sizes 5. Switches, Tube Clamps, Counter protector 6. Case 	8525-0005 Net Price \$1,150
	MXB Everything Demo Includes: <ol style="list-style-type: none"> 1. Demonstrates all three MXB Belt-Drive Actuator carrier styles: Un-guided, Solid Bearing and Profiled Rail 	8525-0089 Net Price \$500
	MX Pneumatic Demo Includes: <ol style="list-style-type: none"> 1. MXP25N (Internal Bearing) Pneumatic Band Cylinder 2. MXP25S (Solid Bearing) Pneumatic Band Cylinder 3. MXP25P (Profiled Rail Bearing) Pneumatic Band Cylinder 4. Counter protector mat 5. Case 	8125-0105 Net Price \$995

Order Today!

Company:	Part Number	Qty.	Net Price Ea.	Price x Qty.
Shipping Address:	<input type="checkbox"/> 3604-0040		\$1,150	
	<input type="checkbox"/> 3604-0039		\$1,150	
	<input type="checkbox"/> 2190-0004		\$ 995	
	<input type="checkbox"/> 2192-0047		\$ 995	
	<input type="checkbox"/> 2750-0189		\$ 875	
Contact Person:	<input type="checkbox"/> 8525-0005		\$1,150	
Phone:	<input type="checkbox"/> 8525-0089		\$ 500	
Purchase Order #	<input type="checkbox"/> 8125-0105		\$ 995	
			Total:	

Demo of Your Choice

Don't see a Demo Kit that fits your needs? Tell us your part number for a 50% discount off of list price for a demo of your choice!

Limited time offer, Contact Tolomatic for details



USA

3800 County Road 116
 Hamel, MN 55340, USA
Phone: (763) 478-8000
Fax: (763) 478-8080
 Toll-Free: **1-800-328-2174**
sales@tolomatic.com
www.tolomatic.com

EUROPE

Tolomatic Europe GmbH
 Zeilweg 42
 60439 Frankfurt am Main
 Germany
Phone: +49 69-2045-7837
EuropeSales@tolomatic.com

CHINA

Tolomatic Automation Products (Suzhou) Co. Ltd.
(ServoWeld® inquiries only)
 No. 60 Chuangye Street, Building 2
 Huqiu District, SND Suzhou
 Jiangsu 215011 - P.R. China
Phone: +86 (512) 6750-8506
Fax: +86 (512) 6750-8507
ServoWeldChina@tolomatic.com

All brand and product names are trademarks or registered trademarks of their respective owners. Information in this document is believed accurate at time of printing. However, Tolomatic assumes no responsibility for its use or for any errors that may appear in



this document. Tolomatic reserves the right to change the design or operation of the equipment described herein and any associated motion products without notice. Information in this document is subject to change without notice.

Visit www.tolomatic.com for the most up-to-date technical information