

INTERNAL BUMPER

Made of urethane composite to prolong cylinder life and reduce noise



DURABLE DESIGN

Tough, lightweight extruded aluminum in a low profile package

DOVETAIL SLOTS

For easy switch mounting

NICKEL-PLATED SHAFTS

Shafts up to 0.625" diameter

MOUNTING FLEXIBILITY

Threaded holes for base or side mounting



DURABLE BEARING

COMPOSITE BEARINGS

- Thin profile allows use of oversize guide rods
- Best choice for impact use or high contaminant environments



ANODIZED ALUMINUM TOOLING PLATE

Threaded bolt thru holes for tooling plate mounting

OPTIONS



STOP COLLAR / BUMPER KIT

- Includes 2 stop collars and 1/4" thick polyurethane external bumpers to help absorb impact shock



DUAL TOOLING PLATE

- Added flexibility for many applications



SWITCHES

- Available in Reed, Hall-effect and Triac
- 15ft. cable with flying leads; available with quick-disconnect couplers