





Tolomatic Demo Kits

All (except MXB Everything) Demo Kits have precut foam for safe transport in durable suitcases.

 <p>The image shows an open black hard-shell suitcase containing a black cylindrical hollow IMA22 actuator, a white cut sheet with technical diagrams, and a black foam insert.</p>	<p>Standard IMA22 Demo Includes:</p> <ol style="list-style-type: none"> 1. Hollow IMA22 (Non-Operational) 2. Features & Benefits Cut Sheet 3. Case 	<p>2722-0718 Net Price \$800</p>
 <p>The image shows an open black hard-shell suitcase containing a stainless steel hollow IMA-S22 actuator, a white cut sheet with technical diagrams, and a black foam insert.</p>	<p>Hygienic IMA-S22 Demo Includes:</p> <ol style="list-style-type: none"> 1. Hollow IMAS22 (Non-Operational) 2. Features & Benefits Cut Sheet 3. Case 	<p>2622-0003 Net Price \$1,500</p>
 <p>The image shows an open black hard-shell suitcase containing a blue roller screw assembly with a nut, a blue foam insert, and a black foam insert.</p>	<p>Roller Screw Demo Includes:</p> <ol style="list-style-type: none"> 1. 20 x 5 Roller Screw sample with Armoloy coating 2. Case 	<p>2750-0189 Net Price \$875</p>
 <p>The image shows an open black hard-shell suitcase containing an RSA24 SNO4 SK6 RP1 actuator, a MAC140 motor with cables, a 5 Amp power supply, and a black foam insert.</p>	<p>RSA Electric Actuator and Power Supply Includes:</p> <ol style="list-style-type: none"> 1. RSA24 SNO4 SK6 RP1 actuator 2. MAC140 motor with cables 3. 5 Amp power supply 4. Case 	<p>1124-0999 Net Price \$1,800</p>

	<p>MX Electric Demo Includes:</p> <ol style="list-style-type: none"> 1. MXE25S Electric Screw-Drive Rodless Actuator 2. MXB25P & 25U Electric Belt-Drive Rodless Actuators 3. Ball & Solid Nut Screw samples, 6 Belt Material samples 4. Cross section of all MX extrusion sizes 5. Switches, Tube Clamps, Counter protector 6. Case 	<p>8525-0005 Net Price \$1,150</p>
	<p>MXB Everything Demo Includes:</p> <ol style="list-style-type: none"> 1. Demonstrates all three MXB Belt-Drive Actuator carrier styles: Un-guided, Solid Bearing and Profiled Rail 	<p>8525-0089 Net Price \$1000</p>
	<p>RSH22 Demo Includes:</p> <ol style="list-style-type: none"> 1. RSH22 Rod-Style Actuator with foot mounts 2. Case 	<p>2122-0999 Net Price \$2,300</p>
	<p>TRS100 Demo Includes:</p> <ol style="list-style-type: none"> 1. TRS100 Rodless Actuator with switch rails 2. 3D printed TRS165 cutaway 3. Case 	<p>0602-0999 Net Price \$1,200</p>

Order Demos from orders@tolomatic.com

Learn more about Tolomatic's products at tolomatic.com/products. Contact your Regional Sales Manager for more information on demo cases and Tolomatic products.



MADE IN U.S.A.

TolomaticTM
EXCELLENCE *IN* MOTION

COMPANY WITH
QUALITY SYSTEM
CERTIFIED BY DNV
= ISO 9001 =
Certified site: Hamel, MN

USA - Headquarters

Tolomatic Inc.
3800 County Road 116
Hamel, MN 55340, USA
Phone: (763) 478-8000
Toll-Free: **1-800-328-2174**
sales@tolomatic.com
www.tolomatic.com

MEXICO

Centro de Servicio
Parque Tecnológico Innovación
Int. 23, Lateral Estatal 431,
Santiago de Querétaro,
El Marqués, México, C.P. 76246
Phone: +1 (763) 478-8000
help@tolomatic.com

EUROPE

Tolomatic Europe GmbH
Elisabethenstr. 20
65428 Rüsselsheim
Germany
Phone: +49 6142 17604-0
help@tolomatic.eu
www.tolomatic.com/de-de

CHINA

**Tolomatic Automation Products
(Suzhou) Co. Ltd.**
No. 60 Chuangye Street, Building 2
Huqiu District, SND Suzhou
Jiangsu 215011 - P.R. China
Phone: +86 (512) 6750-8506
Tolomatic_China@tolomatic.com

All brand and product names are trademarks or registered trademarks of their respective owners. Information in this document is believed accurate at time of printing. However, Tolomatic assumes no responsibility for its use or for any errors

that may appear in this document. Tolomatic reserves the right to change the design or operation of the equipment described herein and any associated motion products without notice. Information in this document is subject to change without notice.

Visit www.tolomatic.com for the most up-to-date technical information